


Specification

Name	Laser Printer		
Model Number	QUALIS-US		
Production Capacity※1	400,000 pcs/hour (Φ7mm, lens tablet, 6 characters, size of one character:W 1.0mm x H 1.0mm)		
Applicable dosage form※2	Film coated tablet, Uncoated tablet, Sugar-coated tablet, Soft capsule		
Electricity	3Φ	AC200V±10%	50/60Hz 13.9KVA (40A)
Compressed air	0.6 MPa	0.8 m³/min	
Vaccum※3	-8 KPa	15m³/min	
Installation enviroment	Temperature: 18 ~ 28 °C, Humidity:45 ~ 65 %RH (no condensation)		
Overall dimension(mm)	1,000 × 1,560 × 1,755 (W×D×H)		
Height of discharge	1,050 mm		
Weight	1,000 kg		
Noise during operation	—		

- ※1 Depends on printing design or shape of dosage form
- ※2 Titanium dioxide is required on the surface film and affects the light and shade of printing.
There are cases where the the products can't be printed depnding on the shape and feature.
The specific specifications correspondense may be required in some cases.
- ※3 The blower is built in the main body.
- *The above information specification is subject to change without prior notice for the technical development.

Overall size (mm)



QUALICAPS, CO., LTD.
321-5 Ikezawacho
Yamatokoriyama
Nara, 639-1032 Japan
Tel: +81 743 57 8920
Fax: +81 743 56 5113
www.qualicaps.com

QUALIS-US

Single surface printing by UV laser


Laser Printer

Printing



Laser printer QUALIS-US

Single surface printing by UV laser



Name of components

1. Hopper
2. UV Laser Scanner
3. Dexter
4. Marking Disk
5. Product discharge chute

- **One of the highest speed UV laser printer**
Production capacity is 400,000 pcs/hour*

*Depends on the size and number of characters


- **Low cost machine**

- **Compact size**
 - QUALIS is more compact than our existing UV laser printer, LIS-250D
 - Built in brower


- **Fewer change parts**
Dexter and O-ring only

- **21 CFR Part 11 Compliance**


Laser Printing Mechanism



The ratio of titanium dioxide(Ti) to oxygen(O) in titanium dioxide is 1:2. UV laser is irradiated on the titanium dioxide then oxygen atom is removed.




The removal of oxygen atom causes change of ratio of titanium atom to oxygen atom. This change of ratio induces the color change of titanium dioxide from white to grey.




No defects caused by ink

No letter shortage, double printing, ink sticking (stain), etc. will occur due to color change of titanium oxide with non-contact UV laser.



Flexible design

Marking letters, mark or logo can be made by CAD which allows flexible design. Test printing and printing result check are not needed before production.



Operating efficiency improvement

Cleaning time is significantly reduced because there is no ink used in the process.




Larger printable area

Not only alphanumeric character's but also katakana and kanji (Chinese characters) are available for printing, resulting in excellent repeatability of details.



No thermal denaturation

Non-thermal effects of the UV Lasers allow for printing without resulting in thermal denaturation on the tablets.



Manufacturing cost reduction

Because no print design roll or ink is needed, those costs are eliminated, as well as the need for extra storage.



Other features

Titanium dioxide is required on the surface film.
Laser marking color is grey
Auto CAD software is attached to this equipment.